

CTS-10465

Deuterium Lamp (2000 hr)
Comparable to: Waters®
WAS081142



Technical Data Sheet

1.0 Description

This deuterium lamp is designed to be compatible with Waters 2487 dual wavelength absorbance detectors, 2488 multichannel absorbance UV/Vis detectors, Acquity UPLC® TUV detectors and nanoAcquity TUV detectors. It is comparable to Waters part number WAS081142.

2.0 Specifications

2.1 Operating Specifications

Lifetime: 2000 hours

2.2 Materials

Socket Contacts: Pre-Tinned Brass
Connector Plug: Nylon, White Color
Lamp Envelope: UV Glass

3.0 Replacement Frequency

It is recommended that the lamp be replaced if it will not ignite, the noise or drift exceeds specifications, or if the lamp energy is below 50% of original intensity, as recorded during the initial installation.

4.0 Installation Information

Sciencix parts are designed to be compatible and interchangeable with OEM parts. Please see instrument service manual for proper removal and installation procedure.



5.0 Warranty

We view your business with us as a partnership based on mutual trust.

We extend a Lifetime Warranty against any manufacturing defects on all Sciencix HPLC repair parts. If a defect is identified, please contact us at 800.682.6480 or by email at sales@sciencix.com to report the issue. We will assist you with a resolution in a timely fashion.