

VersaCap®, VersaBarb®, and Spigot Technology foxxlifesciences.com



- VersaCap® technology provides the flexibility of interchangeable top-connectors
- VersaCap[®] technology is offered in 50mm, 80mm, and 120mm industry standard sizes
- Quick-connect adapters available for easy port changes
- · Leak-proof cap with replaceable gasket
- VersaCap® design enables stacking
- · Available in a variety of configurations
- VersaCap[®], VersaBarb[®], and Spigots are autoclavable
- VersaBarb® offers a convenient solution for bottom-connections and can fit a variety of hose sizes
- Spigot offers two flow rates

Foxx Life Sciences has enhanced the features and benefits of the **EZ**grip[™] carboys and Heavy Duty Vacuum Bottles by offering the **Versa**Cap[®], **Versa**Barb[®], and state-of-the-art spigot technology. These three components expand the wide array of applications supported by the **EZ**grip[™] carboy.

Patented **Versa**Cap[®] is leak-proof, has replaceable platinum-cured silicone gaskets, and provides the ultimate in top-connection flexibility. Open **Versa**Cap[®] is compatible with a variety of adapter inserts, enabling users to quickly change the top connections of each carboy or bottle to match their application needs. **Versa**Cap[®] offers large handles with finger grips that allow for easy tightening and opening. They are also stackable and are offered in 50mm, 80mm (compatible with most carboys), and 120mm wide-mouth versions that fit exclusively on Foxx Life Sciences' 20L, 40L, and 75L **EZ**fil[™] carboys.

Quick-connect hose barb options include quick-connect port combinations of two, three, and four, with $\frac{1}{4}$ " and $\frac{3}{6}$ " hose barb sizes, as well as molded-in hose barb options, available with $\frac{1}{6}$ ", $\frac{1}{4}$ ", $\frac{5}{16}$ ", and $\frac{1}{2}$ " sizes. The Clearview adapter is also available for users who need a crystal-clear window into the carboy for visualizing solution homogenization.

For bottom tubulation options, **Versa**Barb® provides flexibility in drainage, pump connection, filling bell, and automated equipment. **Versa**Barb® is available in ¼", ¾", ½", and ¾" hose barb sizes. A ¾" sanitary fitting **Versa**Barb® is also available to enable the **EZ**grip™ carboy to function as a supply reservoir to a larger system.

Foxx Life Sciences' **EZ**grip™ carboy spigots have large levers that control two flow rates, one for continuous, locked flow and the other for a faster, manual flow. The spigot spout features %" and ¾" hose barbs, and a standard internal luer tape to fit a male barb adapter. The spigot body has internal threads with a hard stop to prevent over-tightening which may damage the seal.

All **Versa**Cap[®], adapters, **Versa**Barb[®], and spigots are made from polypropylene, which may be autoclaved at 15 PSI and 121°C (250°F) for 20 minutes.





VersaCap® Technology

foxxlifesciences.com



2

VersaCap® 50mm

50



205-0313-RLS Cap, Closed Cap Size Hose Barb No. of Quick Qty/pk Size Connects



205-0314-RLS					
Cap, Open with closed adapter					
Cap Size	Hose Barb Size	No. of Quick Connects	Qty/pk		
50	n/a	n/a	2		



205-0317-RLS					
Cap, Open top with adapter, 1/8" HB x 2 and vent					
Cap Size	Hose Barb	No. of Quick	Qty/pk		
	Size	Connects			
50	1/8"	n/a	1		



205-0310-RLS					
Cap, Open top with adapter, 1/4" HB x 2 and vent					
Cap Size	Hose Barb	No. of Quick	Qty/pk		
	Size	Connects			
50	1/4"	n/a	1		



205-0319-RLS				
Cap, Open top with adapter, 5/16" HB x 2 and vent				
Cap Size	Hose Barb Size	No. of Quick Connects	Qty/pk	
50	5/16"	n/a	1	



205-0345	-RLS			
Cap, Vented	top with 0.2	µm Hydrophobic	Membrane	
Cap Size	Hose Barb Size	No. of Quick Connects	Qty/pk	
50	n/a	n/a	1	



205-3331-RLS				
Adapter, Closed				
Cap Size	Hose Barb Size	No. of Quick Connects	Qty/pk	
50	n/a	n/a	1	



205-5331-RLS					
Adapter, ¹ /	8" HB x 2 and	vent			
Cap Size	Hose Barb	No. of Quick	Qty/pk		
	Size	Connects			
50	1/8"	n/a	1		



205-533	2-RLS			
Adapter, ¹	4" HB x 2 and	vent		
Cap Size	Hose Barb Size	No. of Quick Connects	Qty/pk	
50	1/4"	n/a	1	



205-533	3-RLS		
Adapter, 5	/ ₁₆ " HB x 2 and	l vent	
Cap Size	Hose Barb Size	No. of Quick Connects	Qty/pk
50	⁵ / ₁₆ "	n/a	1





VersaCap® Technology foxxlifesciences.com



VersaCap® 80mm



205-1003-RLS Cap, Closed Cap Size Hose Barb No. of Quick Qty/pk Connects 80 2



205-100	4-RLS				
Cap, Open with closed adapter					
Cap Size	Hose Barb Size	No. of Quick Connects	Qty/pk		
80	n/a	n/a	2		



205-1007-RLS					
Cap, Open top with adapter, ¼" HB x 2 and Vent					
Cap Size	Hose Barb	No. of Quick	Qty/pk		
	Size	Connects			
80	1/4"	n/a	1		



205-1008-RLS					
Cap, Open top with adapter, ½" HB x 2 and Vent					
Cap Size	Hose Barb Size	No. of Quick Connects	Qty/pk		
80	1/2"	n/a	1		



205-3001-RLS				
Adapter, C	losed			
Cap Size	Hose Barb Size	No. of Quick Connects	Qty/pk	
80	n/a	n/a	1	



205-300	2-RLS		
Adapter, 1/2	" HB x 2		
Cap Size	Hose Barb Size	No. of Quick Connects	Qty/pk
80	1/."	2	1



205-3003-RLS				
Adapter, 3/4	"HB x 2			
Cap Size	Hose Barb Size	No. of Quick Connects	Qty/pk	
80	3/8"	2	1	



205-300	4-RLS			
Adapter, 1/4	" HB x 3			
Cap Size	Hose Barb Size	No. of Quick Connects	Qty/pk	
80	1/4"	3	1	

-	IJ.	₽,
	1	15
16		1
(3)		

205-300	5-RLS			
Adapter, 3/4	"HB x 3			
Cap Size	Hose Barb Size	No. of Quick Connects	Qty/pk	
80	3/8"	3	1	



205-300	6-RLS		
Adapter, 1/4	"HB x 4		
Cap Size	Hose Barb Size	No. of Quick Connects	Qty/pk
80	1/4"	4	1



205-300	7-RLS			
Adapter, ³ /	's" HB x 4			
Cap Size	Hose Barb Size	No. of Quick Connects	Qty/pk	
80	3/8"	4	1	



	205-500	1-RLS			
	Adapter, 1/4	"HB x 2 and V	ent		
ì	Cap Size	Hose Barb Size	No. of Quick Connects	Qty/pk	
	80	1/4"	n/a	1	



203-300	2-KL3		
Adapter,	1/2" HB x 2 an	nd Vent	
Cap Size	Hose Barb Size	No. of Quick Connects	Qty/pk
80	1/2"	n/a	1



and the same of th			
208-300	1-RLS		
Adapter, Cl	osed Clearvie	w®	
Cap Size	Hose Barb Size	No. of Quick Connects	Qty/pk
80	n/a	n/a	1



VersaCap® Technology

foxxlifesciences.com

Qty/pk



VersaCap® 120mm



205-200	205-2003-RLS				
Cap, Closed					
Cap Size	Hose Barb Size	No. of Quick Connects	Qty/pk		
120	n/a	n/a	2		



205-200	4-RLS		
Cap, Open	with closed ac	dapter	
Cap Size	Hose Barb Size	No. of Quick Connects	Qty/pk
120	n/a	n/a	2



205-400	1-RLS		
Adapter, C	losed		
Cap Size	Hose Barb	No. of Quick	Qty/pk
	Size	Connects	
120	n/a	n/a	1




205-400	2-RLS		
Adapter, 1/2	" HB x 2		
Cap Size	Hose Barb Size	No. of Quick Connects	Qty/pk
120	1/4"	2	1



205-400	3-RLS		
Adapter, ³ / ₂	"HB x 2		
Cap Size	Hose Barb Size	No. of Quick Connects	Qty/pk
120	3/8"	2	1





Refl	205-400	5-R
	Adapter, 3/8 Cap Size	" HE
	120	

205-400	5-RLS			
Adapter, ³ /	s" HB x 3			
Cap Size	Hose Barb Size	No. of Quick Connects	Qty/pk	
120	3/8"	3	1	

Rev (C)		
	1	6

205-4006-RLS				
Adapter, 1/4	" HB x 4			
Cap Size	Hose Barb Size	No. of Quick Connects	Qty/pk	
120	1/4"	4	1	

J	A.
15	1
1	

205-400	7-RLS			
Adapter, ³ /	s" HB x 4			
Cap Size	Hose Barb Size	No. of Quick Connects	Qty/pk	
120	3/8"	4	1	



205-400	8-RLS			
Adapter, E	Z Top [®] adapter			
Cap Size	Hose Barb Size	No. of Quick Connects	Qty/pk	
120	n/a	n/a	1	



foxxlifesciences.com



VersaBarb® and Spigot Technology



225-4001-RLS VersaBarb®, Spigot fitting, closed cap Hose Barb Thread Size Diameter 1 n/a 1 1/8"



225-4002	-RLS		
VersaBarb®,	Spigot fitting,	with 1/4" HB	
Hose Barb Size	Thread Diameter	Qty/pk	
1/4"	1 1/8"	1	



225-4003	-RLS	
Versa Barb [®]	, Spigot fitting,	with 3/8" HB
Hose Barb	Thread	Qty/pk
Size	Diameter	4
3/8"	1 1/8"	- 1




22	5-4004	-RLS	
VersaBarb®, Spigot fitting, with ½" HB			
	se Barb Size	Thread Diameter	Qty/pk
	1/2"	1 1/8"	1

HB = Hose Barb









We recommend testing for your specific application before use.