

HG PRO

PEM Hydrogen generator

The HydroGen series **HG PRO** is able to generate up to 1500 cc/min of Hydrogen with purity better than 99.99999% and pressure up to 16 bar (232 psi). The HG PRO includes a new long life multilayer electrolytic cell with polymeric membrane (PEM) using distilled water. No acid or alkaline solutions are used.

The innovative gas drying system (two-column drying PSA system with automatic regeneration) ensures the maximum grade of hydrogen purity, it is completely maintenance-free and allows continuous operation, 24 hours a day.

The on-board CPU automatically checks for internal leaks and constantly control the operating parameters to guarantee full safety. Up to 20 units can be connected in parallel using an external control box.

The touch-screen LCD interface provides simple and user-friendly management of all functions on the unit.

Main Applications

- Carrier gas for GC and GS-MS
- GC-FID / GC-NPD / GC-FPD / THA
- ICP-MS collision gas
- Refilling metal hydride tanks for use with fuel cells

Main advantages

- ✓ New long life multilayer PEM cell
- ✓ High flow rate up to 1500 cc/min
- ✓ High pressure up to 16 bar (232 psi)
- ✓ RS 232/485 and USB standard
- ✓ LAN optional
- ✓ Auto refill standard
- ✓ High purity: 99.99999%
- ✓ Dryer with no maintenance
- ✓ Safety routine and self monitoring
- ✓ Reduced foot print
- ✓ High pressure GLS electronically controlled (patented)





Specifications

Model: HG PRO	120	180	260	350	500	700	900	1100	1300	1500	
General data											
Electrolytic cell	Long life Multilayer PEM technology										
Drying system	PSA (Pressure Swing Adsorption)										
H2 purity	>99.99999% *1										
Outlet pressure	12 bars (174 psi) / 16 bars (232 psi) (optional)										
H2 flow-rate (Max)	120	180	260	350	500	700	900	1100	1300	1500	
Dimensions (W x D x H)	27 x 44 x 41 cm										
Net weight (no water in tank)	20 Kg			22.5 Kg			25 Kg		26 Kg		
Communication											
RS-232 / USB / RS-485	Standard										
Digital I/O	Standard										
LAN	Optional										
Software functions											
Parallel mode	Ready on board										
Automatic tank refill	Standard										
Fill Hydride canister function	Standard										
Water											
Quality Required	Deionized, ASTM II, <0.1uS										
Supply pressure (min, Max)	0.1 bar (1.45 psi), 0.5 bar (7.25 psi)										
Supply flow rate (min, Max)	0.2 l/min, 1.5 l/min										
Internal tank capacity	3 L										
External tank capacity	5 or 10 L (optional)										
Electrical data											
Type of connection	IEC 320-C14										
Power supply voltage	100-240 Vac (±10%) 50/60 Hz										
Nominal power (Max)	320W			640W				750W			
Fuse rating (5x20mm)	4A (250 Vac – T)			6.3A (250 Vac – T)							
Connections											
Hydrogen outlet	1/8" compression fitting										
Water	Quick release push-in fitting										
Operating/storage conditions											
Working Temperature	5-40°C (41-104°F) *2										
Storage Temperature	1-50°C (34-122°F)										
Humidity (max, non condensing)	70%										
Noise	< 35dB(A)										
IP rating	IP20										
Pollution degree rating	2 (with no aromatic compounds)										
Altitude	< 2000m										

*1 referred to O2, dew point <-75°C (< -103°F), Atmospheric Dew Point (ADP)

*2 with temperature > 35°C (> 95°F) the H2 purity could be less

Ordering codes

Gas Generators

6920.15.012	HG PRO 120
6920.15.018	HG PRO 180
6920.15.026	HG PRO 260
6920.15.035	HG PRO 350
6920.15.050	HG PRO 500
6920.15.070	HG PRO 700
6920.15.090	HG PRO 900
6920.15.105	HG PRO 1100
6920.15.130	HG PRO 1300
6920.15.150	HG PRO 1500

Consumable

6930.00.091	Deionizer water filter
-------------	------------------------



LNI Swissgas

www.lni-swissgas.eu

For further
information or to
trial the equipment,
please contact us:

UVISON

Tel: 01322 285850

Email: info@uvison.com

Uvison Technologies Demo Lab
6 Nepicar Park, London Road, Sevenoaks, Kent TN15 7AF